

PANDUIT™ infrastructure for a connected world

Network Infrastructure Guide





Find the Right Structured Cabling Solution for Enterprise Environments.

Panduit Netkey Solutions

Copper Cable

Part Number	Description
NUL6X04BU-VEG	Category 6A, low smoke zero halogen (LSZH), 4-pair, U/UTP copper cable.
NUC6C04BU-FE	Category 6, PVC (CM), 4-pair, U/UTP, copper cable.



NUC6C04BU-FE

View Product Video

RJ45 Jack Modules

Part Number	Description
NK6X88MBU	Category 6A, 8-position, 8-wire, UTP keystone punchdown jack module.
NK688MBU	Category 6, 8-position, 8-wire, UTP keystone punchdown jack module.



NK688MBU

View Product Details

Patch Panels

Part Number	Description
NKFPL24	Modular Patch Panel, Faceplate with Label, Flat, 24 Port, 1 RU.
NKFPL48	Modular Patch Panel, Faceplate with Label, Flat, 48 Port, 2 RU.



NKFPL24

View Product Details

RJ45 UTP Patch Cords

Part Number	Description
NKU6APC*MBU	Category 6A, UTP patch cord with modular plugs on each end. Blue Color.
NKU6PC*MBU	Category 6, UTP patch cord with modular plugs on each end. Blue Color.

*Remark: * Available metres: 1, 2, 3, 5 or 10 metres.*



NKU6APC*MBU

View Product Details

Faceplates

Part Number	Description
NK^FIWY	Single gang, flush mount vertical faceplate with labels.
NKFPL86F^SAW	Single gang, 86mm x 86mm, shuttered faceplate with label and icon slots.
NKBMIW-X	Module blank, 10 pack. Off white color.

Remark: ^ Available in 1, 2, and 4 port density configurations.



NKFPL86F^SAW

View Product Details

Termination Tools

Part Number	Description
PDT110	Punchdown tool and blade for 110 style IDCs.
CJAST	Copper cable jacket stripping tool.
CWST	Copper cable conductor snipping tool.



PDT110



CJAST

View Product Details

Fiber Optic Cable

Part Number	Description
FLKL9**	9um OS2 Fiber Indoor-Outdoor Tight Buffered Cable, low smoke zero halogen (LSZH), 900um Buffered Fibers.
FLKLX**	50um OM3 Fiber Indoor-Outdoor Tight Buffered Cable, low smoke zero halogen (LSZH), 900um Buffered Fibers.
FLKLZ**	50um OM4 Fiber Indoor-Outdoor Tight Buffered Cable, low smoke zero halogen (LSZH), 900um Buffered Fibers.

*Remark: ** Available Fiber optic core: 04, 06, 08, 12*



FLKL9**

View Product Details

Fiber Optic Termination Enclosures

Part Number	Description
FD1W^^BUDLCZ	Pre-loaded fiber drawer with ^^ LC duplex adapters for 9/125µm (OS1/OS2) singlemode fiber.
FD1W^^AQDLCZ	Pre-loaded fiber drawer with ^^ LC duplex adapters for 50/125µm (OM3/OM4) multimode fiber.
FSC24	Fiber splice chip accommodates and protects up to 24 fusion splices.

Remark: ^^ Available in 12 or 24 port density configurations.



FD1W^^BUDLCZ

View Product Details

Fiber Optic Patch Cords & Pigtails

Part Number	Description
NKFP92ELLLSM***	OS2 LC duplex to LC duplex patch cord, low smoke zero halogen (LSZH), 1.6mm jacket.
NKFPX2ELLLSM***	OM3 LC duplex to LC duplex patch cord, low smoke zero halogen (LSZH), 1.6mm jacket.
NKFPZ22LLLSM***	OM4 LC duplex to LC duplex patch cord, low smoke zero halogen (LSZH), 1.6mm jacket.
NKFP91BN1NNM001	OS2 LC pigtail with 900um buffered fiber, 1 metre.
NKFPX1BN1NNM001	OM3 LC pigtail with 900um buffered fiber, 1 metre.
NKFPZ1BN1NNM001	OM4 LC pigtail with 900um buffered fiber, 1 metre.

*Remark: *** Available metres: 1, 2, 3, 5, 10 metres.*
Example: 001 = 1 metre.



NKFP92ELLLSM***

View Product Details

Open Rack & Vertical Cable Managers

Part Number	Description
R2P	2 post rack, 45 RU, with threaded rails. Black color.
R4P	4 post rack, 45 RU, with threaded rails. Black color.
WMPVHC45E	NetRunner Vertical Cable Manager, front & rear, 45RU.



R2P

View Product Video

Cable Managers

Part Number	Description
WMPFSE	PatchLink™ Horizontal Cable Manager, front only, 1 RU.
WMPF1E	PatchLink™ Horizontal Cable Manager, front only, 2 RU.



WMPFSE

View Product Video

Panduit Singapore
331 North Bridge Road,
#04-02, Odeon Towers,
Singapore 188720

Let's connect.

(C)2024 Panduit. ALL RIGHTS RESERVED. NKT2-ROAP-ENG 07/2024.