




Shielded Copper Cabling System

Innovative Connectivity Solution for
Maximum Performance and Security.

COPPER CABLES



Part Number	Description	View Product Details
PFL6X04BU-CEG	Category 6A F/UTP cable, 23 AWG, Blue, LSZH, 305m	
PFL6004BU-G	Category 6 F/UTP cable, 23 AWG, Blue, LSZH, 305m	
PSL7004WH-HED	Category 7 S/FTP cable, 23 AWG, White, LSZH, 305m	



PFL6X04BU-CEG

*F/UTP for most environment


JACK MODULES

Part Number	Description	View Product Details
CJS6X88TGBUY	Category 6A RJ45 shielded TG termination jack, Blue	
CJS688TGBUY	Category 6 RJ45 shielded TG termination jack, Blue	



CJS6X88TGBUY

PATCH PANEL

Part Number	Description	View Product Details
CP24BLY	24-port all-metal shielded patch panel	
CP48BLY	48-port all-metal shielded patch panel	




CP24BLY



CP48BLY



MODULAR PLUG

Part Number	Description	View Product Details
FPS6X88MTG	Category 6A, shielded field term plug, 26 AWG, Blue	







FPS6X88MTG

PATCH CORDS




Part Number	Description	View Product Details	
S6XPC*MBU	Category 6A, S/FTP patch cord, 26 AWG, Blue		 S6XPC*MBU
S6PC*MBU	Category 6, S/FTP patch cord, 26 AWG, Blue		 S6PC*MBU
STP28X*MBU	Category 6A, F/UTP patch cord, 28 AWG, Blue		 STP28X*MBU

Remark: * Available metres: 1, 2, 3, 5 or 10 metres.



FACEPLATES

Part Number	Description	View Product Details	
CFP86S2IWY	Single gang faceplate, 2 Port, 86x86 Sloped, Off White		 CFP86S2IWY
CFPUKS2SIWY	Single gang faceplate, 2 Port, 86x86 Sloped Shuttered with label, Off White		 CFPUKS2SIWY
CFPL86F2SAW	Single gang faceplate, 2 Port, 86x86 Flat Shuttered with label, Arctic White		 CFPL86F2SAW
CMBIW-X	Blank module, 10 per pack, Off White		 CMBIW-X

TERMINATION TOOLS

Part Number	Description	View Product Details	
EGJT-1	TG Jack and Field Term Plug termination tool, Green		 EGJT-1
CJAST	Copper cable jacket stripping tool		 CJAST
CWST	Copper cable conductor snipping tool		 CWST

BONDING TOOLS

Part Number	Description	View Product Details	
RGCBNJ660P22	Jumper kit, 1.5m long 16mm ² green/yellow insulated cable pre-terminated with two hole lug. Includes copper compression tap		 RGCBNJ660P22
CNBK	Green bonding #12-24 cage nuts and bonding screws, 50/pack		 CNBK



Panduit Singapore
331 North Bridge Road,
#04-02, Odeon Towers,
Singapore 188720

sgp-customer_service@panduit.com
1-800-PANDUIT (Singapore)
1800 801 435 (Malaysia)
001 803 65 7571 (Indonesia)
001 800 65 6385 (Thailand)
000 800 650 1844 / 000 800 650 0369 (India)

Let's connect.

