

# MP75

PXE™ SERIES Mobile Printer

Product Bulletin

## Cost-Effective Network and Electrical Functionality



**PANDUIT™**

**EPSON**  
EXCEED YOUR VISION

PORTABLE LABEL PRINTER PARTNER

## PXE™ SERIES Mobile Printers

Do your job smarter, faster and easier with PXE Series Mobile Printers. This full line of advanced identification printers combine Panduit's industry-leading performance and field-tested durability with Epson's world-class printing technology.



### MP75 Mobile Label Printer

A reliable and affordable printer for network, electrical, and other industrial applications.

#### FEATURES:

- Shared MP Cassette Platform
- 180 dpi print resolution
- Custom Application Specific Label Modes
- Large Library of Barcodes and Custom Symbols
- Prints up to 0.75 in wide labels
- Fast 0.25 in/sec Print Speed
- Continuous Label Cassette
- Qwerty Keyboard
- Backlit LCD Screen
- Manual Push Button Cutter

### Dimensions

#### Compact and Lightweight

- Width: 4.33 in (110 mm)
- Depth: 6.70 in (170 mm)
- Height: 2.20 in (56 mm)

Weight: 14 oz (400 g)  
(excluding batteries, tape cartridge)

### Ordering Information

Part Number	Description
MP75	Compact entry level industrial printer that features custom label modes, a qwerty keyboard, backlit LCD screen, and a large library of barcodes and custom symbols. Includes the lightweight printer, one T075X000VPM-BK continuous label cassette and quick reference card
PTR-CLN	Printer cleaning kit - contains (1) cleaning pen, (8) cleaning solution soaked wipes, (8) foam swabs pre-saturated with cleaning solution, MSDS, and cleaning instructions



PORTABLE LABEL PRINTER PARTNER

#### Epson™ Print Technology

Epson is a global technology leader dedicated to connecting people, things and information with efficient, compact and precision technologies.

#### Panduit™ Labeling and Software Expertise


Panduit creates leading-edge labeling solutions for electrical and network environments, from the data center to the telecom room, the jobsite to the plant floor.

## Ordering Information



### Non-Laminated Label Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Non-laminated adhesive labels for wire/cable identification

 **Nylon Cloth (C1M)**

 **-65°F to 275°F**  
(-54°C to 135°C)


Part Number	Part Description	Printer Compatibility				Print-On Area Color	Height		Length		Std. Pkg. Qty.	Std. Ctn. Qty.
		MP75	MP100	MP200	MP300		In.	mm	Ft.	m		
<a href="#">T050X000C1M-BK</a>	MP Cassette, Continuous Tape, Nylon Cloth, 0.50" W x 19' L, Black on White	Y	N	Y	Y	Black on White	0.465	11.82	19	6	1	5
<a href="#">T075X000C1M-BK</a>	MP Cassette, Continuous Tape, Nylon Cloth, 0.75" W x 19' L, Black on White						0.702	17.82				

Representative offering only, visit [www.panduit.com](http://www.panduit.com) for complete listing of products.



### Continuous Heat Shrink Labels

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Non-adhesive flattened heat shrinkable polyolefin for wire/cable identification

 **Heat Shrinkable Polyolefin**  
**3:1 Heat Shrink Ratio (H1, H2)**

 **-40°F to 257°F**  
(-40°C to 125°C)

Part Number	Part Description	Shrink Ratio	Mil Spec	Printer Compatibility				Ribbon & Material Color	Width		Length		Min. Cable O.D.		Max. Cable O.D.		Wire/Cable Size Range	Std. Pkg. Qty.	Std. Ctn. Qty.
				MP75	MP100	MP200	MP300		In.	mm	Ft.	m	In.	mm	In.	mm			
<a href="#">H000X025H1M</a>	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .25" W x 8' L, White	3:1	Y	Y	Y	Y	Y	Black on White	0.27	6.8	8.2	2.5	0.06	1.4	0.16	4.1	22 - 18 AWG	1	5
<a href="#">H000X025H2M</a>	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .25" W x 8' L, Yellow							Black on Yellow											
<a href="#">H000X034H1M</a>	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .34" W x 8' L, White							Black on White	0.37	9.3	0.07	1.9	0.22	5.7	18 - 12 AWG				
<a href="#">H000X034H2M</a>	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .34" W x 8' L, Yellow							Black on Yellow											


Representative offering only, visit [www.panduit.com](http://www.panduit.com) for complete listing of products.

## Ordering Information



### Continuous Terminal Block Label Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Print terminal block labels ranging in size from 0.24 inches to 0.38 inches

 Polyolefin (FJM)

 -40°F to 180°F (-40°C to 82°C)


Part Number	Part Description	Printer Compatibility				Print-On Area Color	Height		Length		Std. Pkg. Qty.	Std. Ctn. Qty.
		MP75	MP100	MP200	MP300		In.	mm	Ft.	m		
<a href="#">T024X000FJM-BK</a>	MP Cassette, Continuous Tape, Polyolefin, 0.24" W x 23' L, Black on White					Black on White	0.229	5.82	23	7	1	5
<a href="#">T038X000FJM-BK</a>	MP Cassette, Continuous Tape, Polyolefin, 0.38" W x 23' L, Black on White	Y	Y	Y	Y		0.347	8.82				


Representative offering only, visit [www.panduit.com](http://www.panduit.com) for complete listing of products.



### Continuous Tape Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Print custom pipe markers, voltage markers, signs, bin markers, and network ID labels on demand
- For flat label applications only


 Vinyl Material (VXM & VPM)

 -40°F to 194°F (-40°C to 90°C)

 Polyester Material (YKM & BYM)

 -40°F to 257°F (-40°C to 125°C)

 Magnetic Material (MPM & MXM)

 14°F to 104°F (-10°C to 40°C)

Part Number	Part Description	Printer Compatibility				Ribbon & Material Color	Width		Length		Std. Pkg. Qty.	Std. Ctn. Qty.		
		MP75	MP100	MP200	MP300		In.	mm	Ft.	m				
<a href="#">T038X000VPM-BK</a>	MP Cassette, Continuous Tape, Vinyl, 0.38" W x 23' L, Black on White.	Y	Y	Y	Y	Black on White	0.354	9.0	23	7.0	1	5		
<a href="#">T038X000VXM-BK</a>	MP Cassette, Continuous Tape, Vinyl, 0.38" W x 23' L, Black on Yellow.					Black on Yellow								
<a href="#">T038X000YKM-BK</a>	MP Cassette, Continuous Tape, Polyester, 0.38" W x 30' L, Black on Clear.					Black on Clear	30	9.1						
<a href="#">T038X000BYM-WH</a>	MP Cassette, Continuous Tape, Polyester, 0.38" W x 30' L, White on Black.					White on Black								
<a href="#">T050X000VPM-BK</a>	MP Cassette, Continuous Tape, Vinyl, 0.50" W x 23' L, Black on White.					Black on White	0.472	12.0	23	7.0				
<a href="#">T050X000VXM-BK</a>	MP Cassette, Continuous Tape, Vinyl, 0.50" W x 23' L, Black on Yellow.					Black on Yellow								
<a href="#">T050X000YKM-BK</a>	MP Cassette, Continuous Tape, Polyester, 0.50" W x 30' L, Black on Clear.					Black on Clear							30	9.1
<a href="#">T050X000BYM-WH</a>	MP Cassette, Continuous Tape, Polyester, 0.50" W x 30' L, White on Black.					White on Black								
<a href="#">T075X000VPM-BK</a>	MP Cassette, Continuous Tape, Vinyl, 0.75" W x 23' L, Black on White.					Black on White	0.710	18.0	23	7.0				
<a href="#">T075X000VXM-BK</a>	MP Cassette, Continuous Tape, Vinyl, 0.75" W x 23' L, Black on Yellow.					Black on Yellow								
<a href="#">T075X000YKM-BK</a>	MP Cassette, Continuous Tape, Polyester, 0.75" W x 30' L, Black on Clear.					Black on Clear							30	9.1
<a href="#">T075X000BYM-WH</a>	MP Cassette, Continuous Tape, Polyester, 0.75" W x 30' L, White on Black.					White on Black								

### PXE SERIES



**MP300/E**



**MP200**



**MP100/E**



**MP75**

#### EMEA SALES OFFICES AND BRIEFING CENTERS

**London, United Kingdom**

One Oliver's Yard  
55-71 City Rd,  
Old Street,  
London EC1Y 1HQ  
Tel: +44 208  
601 7200

**Schwalbach, Germany**

Am Kronberger  
Hang 8  
65824 Schwalbach  
Tel: + 49 69  
770626180

**Milan, Italy**

Via Lepetit, 40,  
20020 Lainate  
Tel: +39 0293 17 31

**Brussels, Belgium**

Fountain Plaza,  
Belgicastraat 3  
1930 Zaventem  
Tel: +32 02  
466 86 60

**Moscow, Russia**

B. Serpukhovskaya,  
25 bld. 1  
115093 Moscow  
Tel: +7 499  
236 1441

**Arad, Romania**

Strada Ovidiu FN,  
Arad 310163,  
Tel: +40 357  
100 210

**Dubai, UAE**

3305 Shatha Tower  
Dubai Media City  
Dubai  
Tel: +971 4 3616933

**Doha, Qatar**

Al Mana Twin  
Towers, Office  
A, 12th floor,  
C-Ring Road, Doha  
Tel: +974 4491 0383

#### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

**PANDUIT EUROPE LTD.**

London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

**PANDUIT CANADA**

Markham, Ontario  
cs-cdn@panduit.com  
Phone: 800.777.3300

**PANDUIT SINGAPORE PTE. LTD.**

Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

**PANDUIT JAPAN**

Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

**PANDUIT LATIN AMERICA**

Guadalajara, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

**PANDUIT AUSTRALIA PTY. LTD.**

Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information  
Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs-emea@panduit.com](mailto:cs-emea@panduit.com)  
or by phone: +44 208 601 7200