

## Panduit™ PXE Mobile Solutions deliver high quality products that help you do your job smarter, faster and easier.

These solutions combine Epson's world-class printing technology with Panduit's industry-leading performance and field-tested durability. This full line of Electrical and Network label printers provides the solution that's best for you, from on-site smaller jobs to on-demand high volume label printing projects.









FEATURES				
PART NUMBER	<u>MP75</u>	<u>MP100</u>	<u>MP200</u>	<u>MP300</u>
Price	\$	\$\$	\$\$	<b>\$\$\$</b>
<b>Automatic Cutter</b>		Ø	Ø	$\bigcirc$
Half-Cut Feature			$oldsymbol{\lozenge}$	$\bigcirc$
PC Interface and Printing for Easy-Mark Plus™ Software		Ø	Ø	Ø
Bluetooth/Wi-Fi/Mobile App Compatible		Ø		
Maximum Continuous Label Media Width	0.75 in.	1.0 in.	1.0 in.	1.5 in.
Print Speed	0.25 lps	0.6 lps	1.2 lps	1.4 lps
Weight	0.9 lbs.	1.3 lbs.	2.4 lbs.	2.7 lbs.
Size	4.4 in. W x 2.8 in. H x 6.7 in. L	2.36 in. W x 5.9 in. H x 5.4 in. L	5.4 in. W x 3.5 in. H x 11.6 in. L	5.4 in. W x 3.8 in. H x 11.6 in. L
Print Resolution	180 dpi	180 dpi	180 dpi	360 dpi
LABEL TYPES				
Continuous Vinyl & Polyester Tapes	Ø	Ø	Ø	Ø
Continuous Heat Shrink Tubing	Ø	Ø	Ø	Ø
Continuous Self- Laminating Labels		Ø	Ø	Ø
Continuous Magnetic Tape		Ø	Ø	Ø
Die-Cut Self-Laminating Labels				Ø
Die-Cut Component Labels				Ø
Turn-Tell <sup>™</sup> Labels				igoremsize

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

© 2021 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. IDSG2--SA-ENG 11/2021 For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300



